Features	<ul> <li>10W DIP24 Package</li> <li>2KVDC and 3kVDC Isolation Options</li> <li>2:1 and 4:1 Versions</li> </ul>
Regulated	Continuous Short Circuit Protection
Converters	<ul> <li>(power limiting)</li> <li>Synchronous Rectification on 3.3, 5V outputs</li> <li>Full SMD internal design</li> </ul>
	Through Hole or SMD Pinning Options
	<ul> <li>Remote Control Pin</li> <li>Efficiency to 87%</li> </ul>

**Description** The REC10-xxxxSRW/DRW-series offer single and dual regulated outputs in a DIP24 package with 2kV or 3kV isolation options and are suitable for higher power industrial or medical applications. Remote on/off control is standard and SMD pinning is offered with the **/SMD** option. The converters can deliver 150% rated power for short periods of time to cope with applications with large capacitive loads or high start up currents.

Selection Guide					
Part Number	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (%)	Max. Cap. Load
	. ,		× ,		
REC10-xx3.3SRW/H*/A/M	9-18, 18-36, 36-75	3.3	2000	84-85	2200µF
REC10-xx05SRW/H*/A/M	9-18, 18-36, 36-75	5	2000	86-87	2200µF
REC10-xx12SRW/H*/A/M	9-18, 18-36, 36-75	12	833	85-86	470µF
REC10-xx15SRW/H*/A/M	9-18, 18-36, 36-75	15	667	85-86	220µF
REC10-xx05DRW/H*/A/M	9-18, 18-36, 36-75	±5	±1000	84	±1000µF
REC10-xx12DRW/H*/A/M	9-18, 18-36, 36-75	±12	±416	86	±220µF
REC10-xx15DRW/H*/A/M	9-18, 18-36, 36-75	±15	±333	86	±100µF
REC10-xx3.3SRWZ/H*/A/M	9-36, 18-75	3.3	2000	84	2200µF
REC10-xx05SRWZ/H*/A/M	9-36, 18-75	5	2000	86	2200µF
REC10-xx12SRWZ/H*/A/M	9-36, 18-75	12	833	85	470µF
REC10-xx15SRWZ/H*/A/M	9-36, 18-75	15	667	85	220µF
REC10-xx05DRWZ/H*/A/M	9-36, 18-75	±5	±1000	83	±1000µF
REC10-xx12DRWZ/H*/A/M	9-36, 18-75	±12	±416	85	±220µF
REC10-xx15DRWZ/H*/A/M	9-36, 18-75	±15	±333	85	±100µF
* Standard is /H2 for 2kVDC isol	ation,	2:	1		4:1
use /H3 for 3kVDC Isolation (n	ot SMD)	xx = 9-18Vin	= 12,		6Vin = 24,
* add suffix "/X2" for pinning op	tions, see next page.	xx = 18-36Vi	n = 24,	xx = 18-3	75Vin = 48
* add suffix " <b>/SMD</b> " for SMD pac REC10-2405SRW/H2/A/M/SN	0 . 0	xx = 36-75Vi	n = 48		

## **Specifications** (measured at $T_A = 25^{\circ}$ C, nominal input voltage, full load and after warm-up)

Input Voltage Range		2:1 & 4:1
Input Filter		PI Network
Output Voltage Accuracy		±1.5% max.
Line Voltage Regulation (VL to VH a	at full load)	±0.5% max.
Load Voltage Regulation	Single	±0.5% max.
(25% to 100% full load)	Dual	±1.2% max.
Cross Regulation (100%: 25% to	100% full load )	±5% max.
Output Ripple and Noise (with 100n output capacitor and 20MHz BW)		100mVp-p max.
Start-up time		300ms typ.
Operating Frequency (Full Load)		400kHz typ.
Efficiency at Full Load		see Selection Guide
Minimum Load		0%
		continued on next page

**ECONOLINE** 

DC/DC-Converter with 3 year Warranty



## 10 Watt DIP24 & SMD Single & Dual Output



RoHS 2011/65/EU 6/6

c EUs

EN-60950-1 Certified EN-60601-1 Certified UL-60950-1 Certified

REC10

\*\*Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.

**Refer to Application Notes** 

# REC10-S\_DRW(Z)/H\*/A/M Series


## **Specifications** (measured at $T_A = 25^{\circ}$ C, nominal input voltage, full load and after warm-up)

**ECONOLINE** DC/DC-Converter

## **Derating-Graph**


(Ambient Temperature)

2:1 Converters






## 4:1 Converters




,		12V Ir	•		36VDC
		24V Ir	•		50VDC
		48V Ir			100VDC
Isolation Voltage	H2-Suffix and SMD		d for 1 second)		2000VDC
			for 1 minute**)		1000VAC / 60Hz
	H3-Suffix		d for 1 second)		3000VDC
		(rated	for 1 minute**)		1500VAC / 60Hz
Isolation Capacitan					1200pF typ.
Isolation Resistance	<del>)</del>				1 G $\Omega$ min.
Overload Protection	1				150% typ.
Short Circuit Protec	tion				tinuous, Auto Restart
Operating Tempera	ture Range	4:1		-40°C t	o +71°C (see Graph)
(free air convection	)	2:1		-40°C t	o +81°C (see Graph)
Remote On/Off		DC/D0	CON	0	pen or 3.5V <vr<12v< td=""></vr<12v<>
		DC/D0	C OFF	:	Short or OV <vr<1.2v< td=""></vr<1.2v<>
Storage Temperatu	re Range				-55°C to +105°C
Temperature Coeffi	cient				±0.05% max.
Relative Humidity					95% RH
Case Material			Nickel Plated	Metal with I	Non-Conductive Base
Thermal Impedance	e	Natura	al convection		15°C/W
Maximum Case Ter	nperature				100°C
Vibration			10-	·55Hz, 2G, 3	30mins along X,Y & Z
Package Weight					18g
Packing Quantity					15 pcs per Tube
MTBF (+25°C) ך	Detailed Information see		using MIL-HDBK	217F	1000 x 10 <sup>3</sup> hours
	Application Notes chapter "M	ITBF"	using MIL-HDBK		>250 x 10 <sup>3</sup> hours
Certifications			-		
EN General Safety	Report: SPCLVD12110	)33-2		EN60950	-1:2006 + A12:2011
UL General Safety	Report: E224736				UL 60950-1 1st Ed.
· · · · · · · · · · · · · · · · · · ·				C2	2.2 No. 60950-1-03
EN Medical Safety	Report: MDD1206058		11206085		60601-1 3rd Edition
LIN INICUICAL SALELY	1200000 ועשאו	VIN + U			
			iviedical Repo	nτ + ISU149	971 Risk Assessment

**Typical Characteristics** 

## REC10-12055RW/H2/A/M (/SMD) REC10-12125RW/H2/A/M (/SMD)



Efficiency VS Input Voltage




Note: Refer to Application Notes for EMC Class B Filter suggestion




## REC10-S\_DRW(Z)/H\*/A/M Series


Package Style and Pinning (mm)


### 24 PIN DIP Package - Available with /H2 and /H3 Options





#### **Recommended Footprint Details**






Pin Connections DIP24

Pin #	Single	Single/X2	Dual
1	CTRL	No Pin	CTRL
2	–Vin	–Vin	–Vin
3	–Vin	-Vin	–Vin
9	NC	No Pin	Com
11	NC	NC	–Vout
14	+Vout	+Vout	+Vout
16	- Vout	-Vout	Com
22	+Vin	+Vin	+Vin
23	+Vin	+Vin	+Vin
NC = No	Connection		

XX.X  $\pm 0.5$  mm XX.XX  $\pm$  0.25 mm

### 24 PIN SMD Package- Only available with /H2 Option



		19.90	
1 0.90			
<u>م_ا</u>			 ا اگر
	•	20.30	 
-		25.40	 

\		→ + 1.54	2.03
.67	Top View	I	
24.64			
	1		
, <u>↓</u>	-00000		
	27.94		

### **Pin Connections DIP24 SMD**

Pin #	Single	Dual
1	CTRL	CTRL
2	-Vin	–Vin
3	-Vin	–Vin
9	NC	Com
11	NC	-Vout
14	+Vout	+Vout
16	– Vout	Com
22	+Vin	+Vin
23	+Vin	+Vin
4,5,10,12		NC
13,15,20,21,24		NC
NC = No Connection		
	0.5 mm 0.25 mm	

REC10

The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflit bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.