

# Test Report

RECOM DEVELOPMENT & TRADING GMBH & CO KG  
TECHNOLOGIEZENTRUM SALZKAMMERGUT  
KROTTENSEESTR. 45, 4810 GMUNDEN  
AUSTRIA

Report No. : CE/2005/30154G  
Date : 2005/03/16  
Page : 1 of 3

**The following merchandise was (were) submitted and identified by the client as :**

Type of Product : DC-DC CONVERTERS  
Style/Item No : RP08 SERIES  
Sample Received : 2005/03/01  
Testing Date : 2005/03/01 TO 2005/03/16

=====  
**Test Result** : - Please see the next page -

  
Daniel Yeh, M.R. / Operation Manager  
Signed for and on behalf of  
SGS TAIWAN LTD.

# Test Report

RECOM DEVELOPMENT & TRADING GMBH & CO KG  
 TECHNOLOGIEZENTRUM SALZKAMMERGUT  
 KROTTENSEESTR. 45, 4810 GMUNDEN  
 AUSTRIA

Report No. : CE/2005/30154G  
 Date : 2005/03/16  
 Page : 2 of 3

## Test Result

PART NAME NO.1 : MIXED ALL PARTS(DC-DC CONVERTERS)

Test Item (s):	Unit	Method	MDL	Result
				No.1
Monobromobiphenyl	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl	%		0.0005	N.D.
Tribromobiphenyl	%		0.0005	N.D.
Tetrabromobiphenyl	%		0.0005	N.D.
Pentabromobiphenyl	%		0.0005	N.D.
Hexabromobiphenyl	%		0.0005	N.D.
Heptabromobiphenyl	%		0.0005	N.D.
Octabromobiphenyl	%		0.0005	N.D.
Nonabromobiphenyl	%		0.0005	N.D.
Decabromobiphenyl	%		0.0005	N.D.
<b>Total PBBs (Polybrominated biphenyls)/Sum of above</b>	%		-	N.D.
Monobromobiphenyl ether	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl ether	%		0.0005	N.D.
Tribromobiphenyl ether	%		0.0005	N.D.
Tetrabromobiphenyl ether	%		0.0005	N.D.
Pentabromobiphenyl ether	%		0.0005	N.D.
Hexabromobiphenyl ether	%		0.0005	N.D.
Heptabromobiphenyl ether	%		0.0005	N.D.
Octabromobiphenyl ether	%		0.0005	0.0040
Nonabromobiphenyl ether	%		0.0005	0.0129
Decabromobiphenyl ether	%		0.0005	0.0283
<b>Total PBBEs(PBDEs) (Polybrominated biphenyl ethers)/Sum of above</b>	%		-	0.0452

# Test Report

RECOM DEVELOPMENT & TRADING GMBH & CO KG  
 TECHNOLOGIEZENTRUM SALZKAMMERGUT  
 KROTTENSEESTR. 45, 4810 GMUNDEN  
 AUSTRIA

Report No. : CE/2005/30154G  
 Date : 2005/03/16  
 Page : 3 of 3

Test Item (s):	Unit	Method	MDL	Result
				No.1
Chromium VI (Cr+6)	ppm	As per US EPA 7196A and US EPA 3060A.	2	N.D.
Cadmium (Cd)	ppm	ICP-AES after as per EN 1122, method B:2001 or other acid digestion.	2	N.D.
Mercury (Hg)	ppm	ICP-AES after as per US EPA 3052 or other acid digestion.	2	N.D.
Lead (Pb)	ppm	ICP-AES after as per US EPA 3050B or other acid digestion.	2	751.5

NOTE: (1) N.D. = Not detected (<MDL)  
 (2) ppm = mg/kg  
 (3) MDL = Method Detection Limit  
 (4) " - " = No Regulation